

# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Preassembled relay module with Push-in connection, consisting of: relay base, power contact relay, plug-in display/interference suppression module, and retaining bracket. Contact switching type: 2 changeover contacts. Input voltage: 120 V AC

## Product description

The pluggable electromechanical and solid-state relays in the RIFLINE complete product range and the base are recognized and approved in accordance with UL 508. The relevant approvals can be called up at the individual components in question.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2903311       |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | C465          |
| Product key                          | DK652A        |
| GTIN                                 | 4046356732512 |
| Weight per piece (including packing) | 109.7 g       |
| Weight per piece (excluding packing) | 109.7 g       |
| Customs tariff number                | 85364900      |
| Country of origin                    | CN            |

# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

## Set consists of

### RIF-2-BPT/4X21 - Relay base

2900934

<https://www.phoenixcontact.com/us/products/2900934>



Relay base RIF-2..., for industrial relay with 2 or 4 changeover contacts, Push-in connection, plug-in option for input/interference suppression modules, for mounting on NS 35/7,5

---

### REL-IR2/L-120AC/2X21 - Single relay

2903667

<https://www.phoenixcontact.com/us/products/2903667>



Plug-in industrial relay with power contacts, 2 changeover contacts, test button, status LED, mechanical switching position indicator, input voltage: 120 V AC

## RIF-2-RPT-LV-120AC/2X21 - Relay module

2903311

<https://www.phoenixcontact.com/us/products/2903311>



## RIF-V-120-230 UC - Plug-in module

2900948

<https://www.phoenixcontact.com/us/products/2900948>



Plug-in module, for mounting on RIF-1, RIF-2, RIF-3, and RIF-4, with varistor, input voltage: 120 V AC ... 230 V AC / DC  $\pm 20\%$

---

## RIF-RH-2 - Retaining bracket

2900954

<https://www.phoenixcontact.com/us/products/2900954>



Relay retaining bracket, with ejector function and holder for marking material, suitable for RIF-2 relay base, for industrial relay

## Technical data

### Product properties

|                         |                                |
|-------------------------|--------------------------------|
| Product type            | Relay Module                   |
| Product family          | RIFLINE complete               |
| Application             | Universal                      |
| Operating mode          | 100% operating factor          |
| Mechanical service life | approx. $2 \times 10^7$ cycles |

### Insulation characteristics

|                      |                                |
|----------------------|--------------------------------|
| Insulation           | Basic insulation               |
| Overvoltage category | III                            |
| Pollution degree     | 2 (Rated voltage of 230/400 V) |

### Data management status

|                              |            |
|------------------------------|------------|
| Date of last data management | 20.01.2026 |
|------------------------------|------------|

### Electrical properties

|   |  |
|---|--|
| Maximum power dissipation for nominal condition | 1.56 W   |
| Test voltage (Winding/contact)                  | 2.5 kV <sub>rms</sub> (50 Hz, 1 min., winding/contact) |
| Test voltage (Contact/contact)                  | 2.5 kV <sub>rms</sub> (50 Hz, 1 min., contact/contact) |
| Rated insulation voltage                        | 250 V AC   |
| Rated surge voltage                             | 4 kV   |

### Input data

#### Coil side

|   |                              |
|---|------------------------------|
| Nominal input voltage $U_N$               | 120 V AC                     |
| Input voltage range                       | 96 V AC ... 144 V AC (20 °C) |
| Input voltage range in reference to $U_N$ | see diagram                  |
| Mains frequency                           | 50/60 Hz                     |
| Drive and function                        | monostable                   |
| Drive (polarity)                          | polarized                    |
| Typical input current at $U_N$            | 13 mA                        |
| Typical response time                     | 5 ms ... 15 ms               |
| Typical release time range                | 5 ms ... 20 ms               |
| Coil voltage                              | 120 V AC                     |
| Protective circuit                        | Varistor                     |
| Operating voltage display                 | Yellow LED                   |

### Output data

#### Switching

|                        |                       |
|------------------------|-----------------------|
| Contact switching type | 2 changeover contacts |
| Type of switch contact | Single contact        |

# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

|                                       |  |
|---------------------------------------|--|
| Contact material                      | AgNi   |
| Maximum switching voltage             | 250 V AC/DC  |
| Minimum switching voltage             | 5 V (24 mA)  |
| Limiting continuous current           | 8.5 A (see diagram)  |
| Maximum inrush current                | 30 A (20 ms, N/O contacts)   |
| Min. switching current                | 5 mA (24 V)  |
| Interrupting rating (ohmic load) max. | 204 W (at 24 V DC)<br>124 W (at 48 V DC)<br>108 W (at 60 V DC)<br>52 W (at 110 V DC)<br>48 W (at 220 V DC)<br>2125 VA (for 250 V AC) |
| Switching capacity                    | 2 A (at 24 V, DC13)<br>0.22 A (at 120 V, DC13)<br>0.11 A (at 250 V, DC13)<br>3 A (at 120 V, AC15)<br>1.5 A (at 240 V, AC15)          |

## Connection data

|                                  |   |
|----------------------------------|---|
| Connection method                | Push-in connection  |
| Stripping length                 | 8 mm  |
| Conductor cross-section rigid    | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>  |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup><br>0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (Ferrule with plastic sleeve)<br>0.14 mm <sup>2</sup> ... 1 mm <sup>2</sup> (Ferrule with plastic sleeve, two conductors on double terminal block) |
| Conductor cross-section AWG      | 26 ... 16 (solid)<br>26 ... 16 (flexible)   |

## Dimensions

### Item dimensions

|        |       |
|--------|-------|
| Width  | 31 mm |
| Height | 96 mm |
| Depth  | 75 mm |

### Drill hole

|          |        |
|----------|--------|
| Diameter | 3.2 mm |
|----------|--------|

## Material specifications

|  |                 |
|--|-----------------|
| Color  | gray (RAL 7042) |
| Flammability rating according to UL 94 (Housing) | V2 (Housing)    |

## Environmental and real-life conditions

### Ambient conditions

# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

|   |                   |
|---|-------------------|
| Degree of protection (Relay base)       | IP20 (Relay base) |
| Degree of protection (Relay)            | RT I (Relay)      |
| Ambient temperature (operation)         | -40 °C ... 50 °C  |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C  |

## Approvals

### Corrosive gas test

|                |                            |
|----------------|----------------------------|
| Identification | ISA-S71.04. G3 Harsh Group |
|                | EN 60068-2-60              |

## Standards and regulations

|                       |               |
|-----------------------|---------------|
| Standards/regulations | IEC 60947-5-1 |
|-----------------------|---------------|

## Mounting

|                   |                           |
|-------------------|---------------------------|
| Mounting type     | DIN rail mounting         |
| Assembly note     | in rows with zero spacing |
| Mounting position | any                       |

## Drawings

Diagram



① DC coil (observe contact derating)

② AC coil (observe contact derating)

Operating voltage range


Diagram



- ① AC, ohmic load
- ② DC, ohmic load

Interrupting rating

Diagram



Contact derating

Diagram



① 250 V AC, Ohmic load

Electrical service life

Diagram



Service life reduction factor



Permissible humidity for operation and storage.

The maximum permissible ambient temperature as specified in the data sheet must be observed.

Area A: Ice buildup at ambient temperatures  $\leq 0^\circ\text{C}$  must be prevented

Area B: Condensation at ambient temperatures  $> 0^\circ\text{C}$  must be prevented

On 30 full days that are naturally distributed across an entire year, a humidity level of 95% is permissible at an ambient temperature  $\leq 25^\circ\text{C}$ .


# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

Circuit diagram



AC coils

# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2903311>



**CSA**

Approval ID: 76787



**CCC**

Approval ID: 2024010303656841

**DNV**

Approval ID: TAA000018V

# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371601 |
| ECLASS-15.0 | 27371601 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001437 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122300 |
|-------------|----------|

# RIF-2-RPT-LV-120AC/2X21 - Relay module



2903311

<https://www.phoenixcontact.com/us/products/2903311>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 2.061 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)