


DTMED 6 - Feed-through terminal block



3034413

<https://www.phoenixcontact.com/us/products/3034413>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block, nom. voltage: 500 V, nominal current: 41 A, number of connections: 2, connection method: Leg spring connection, Rated cross section: 6 mm², cross section: 0.5 mm² - 10 mm², mounting type: NS 35/7,5, NS 35/15, color: gray

Commercial data

Item number	3034413
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BE22
Product key	BE2233
GTIN	4046356151832
Weight per piece (including packing)	21.63 g
Weight per piece (excluding packing)	20.694 g
Customs tariff number	85369010
Country of origin	PL

DTMED 6 - Feed-through terminal block



3034413

<https://www.phoenixcontact.com/us/products/3034413>

Technical data

Product properties

Product type	Feed-through terminal block
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
---------------------	------

Connection data

Number of connections per level	2
Nominal cross section	6 mm ²
Connection method	Leg spring connection
Stripping length	12 mm
Internal cylindrical gage	A5
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	0.5 mm ² ... 10 mm ²
Cross section AWG	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 6 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	0.5 mm ² ... 1.5 mm ²
Nominal cross section	6 mm ²
Nominal current	41 A
Maximum load current	30 A (with 10 mm ² conductor cross-section)
Nominal voltage	500 V

Connection cross sections directly pluggable

Conductor cross-section rigid	0.5 mm ² ... 10 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 6 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²

Dimensions

Width	8.2 mm
Height	49.6 mm

Material specifications

DTMED 6 - Feed-through terminal block



3034413

<https://www.phoenixcontact.com/us/products/3034413>

Color	gray
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Electrical tests

Surge voltage test

Test voltage setpoint	9.8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 6 mm ²	0.72 kA
Short-time withstand current 10 mm ²	1.2 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2.2 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Mechanical tests

Mechanical strength

Result	Test passed
--------	-------------

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	5 N

DTMED 6 - Feed-through terminal block



3034413

<https://www.phoenixcontact.com/us/products/3034413>

Result	Test passed
--------	-------------

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	0.5 mm ² / 0.3 kg
	6 mm ² / 1.4 kg
	10 mm ² / 2 kg
Result	Test passed

Environmental and real-life conditions

Aging

Temperature cycles	192
Result	Test passed

Needle-flame test

Time of exposure	30 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Spectrum	Long life test category 1, class B, body mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	1.857 (m/s ²)/Hz
Acceleration	0.8g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Standards and regulations

Connection in acc. with standard	IEC 60947-7-1
----------------------------------	---------------

Mounting

Mounting type	NS 35/7,5
	NS 35/15


DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>

Drawings

Connection diagram




DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>



Connection diagram




DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>



Connection diagram




with PE terminals having the same contours

DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>

Connection diagram




phase to phase

DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>

Schematic diagram




Simple three-phase current transformer set

DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>

Schematic diagram




Interlinked three-phase current transformer set

DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>

Schematic diagram



Interlinked three-phase current transformer set with grounded star point

DTMED 6 - Feed-through terminal block


3034413

<https://www.phoenixcontact.com/us/products/3034413>

Circuit diagram



Circuit diagram




DTMED 6 - Feed-through terminal block



3034413

<https://www.phoenixcontact.com/us/products/3034413>

Circuit diagram




DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>

Circuit diagram




DTMED 6 - Feed-through terminal block

3034413

<https://www.phoenixcontact.com/us/products/3034413>

Circuit diagram



DTMED 6 - Feed-through terminal block



3034413

<https://www.phoenixcontact.com/us/products/3034413>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com