

PTMED 6-CT/1P-PE - Protective conductor terminal block




3212302

<https://www.phoenixcontact.com/us/products/3212302>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective conductor terminal block, connection method: Push-in connection, 1 level, cross section: 0.5 mm² - 10 mm², color: green-yellow



Product description

Test disconnect terminal block with plug-in zone for current transformer short circuit plug PPCT 6/...

Commercial data

Item number	3212302
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE22
Product key	BE2233
GTIN	4046356623193
Weight per piece (including packing)	27.605 g
Weight per piece (excluding packing)	27.605 g
Customs tariff number	85369010
Country of origin	PL

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Technical data

Product properties

Product type	Ground terminal block
Product family	PTME
Number of connections	2
Number of rows	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	1.31 W

Connection data

Grounding foot	Yes
Number of connections per level	2
Nominal cross section	6 mm ²

1 level

Connection method	Push-in connection
Note	Please observe the current carrying capacity of the DIN rails.
Stripping length	12 mm
Internal cylindrical gage	A5
Connection in acc. with standard	IEC 61984
Conductor cross-section rigid	0.5 mm ² ... 10 mm ²
Cross section AWG	20 ... 8 (converted acc. to IEC)
Conductor cross-section flexible	0.5 mm ² ... 6 mm ²
Conductor cross-section, flexible [AWG]	20 ... 10 (converted acc. to IEC)
Conductor cross-section flexible (ferrule without plastic sleeve)	0.5 mm ² ... 6 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	0.5 mm ² ... 6 mm ²
Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve)	0.5 mm ² ... 1.5 mm ²

1 level Connection cross sections directly pluggable

Conductor cross-section rigid	1 mm ² ... 10 mm ²
Conductor cross-section flexible (ferrule without plastic sleeve)	1 mm ² ... 6 mm ²
Flexible conductor cross-section (ferrule with plastic sleeve)	1 mm ² ... 6 mm ²

Dimensions

Width	8.2 mm
End cover width	2.2 mm
Height	114.9 mm

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Depth on NS 35/7,5	49.6 mm
Depth on NS 35/15	57.1 mm

Material specifications

Color	green-yellow
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Service life

Insertion/withdrawal cycles	100
-----------------------------	-----

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Spectrum	Long life test category 1, class B, body mounted
Frequency	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
ASD level	$1.857 \text{ (m/s}^2\text{)}^2\text{/Hz}$
Acceleration	0.8g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Specification	DIN EN 50155 (VDE 0115-200):2008-03
Pulse shape	Half-sine
Acceleration	5g
Shock duration	30 ms

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 61984
----------------------------------	-----------

Mounting

Mounting type	NS 35/7,5
	NS 35/15

PTMED 6-CT/1P-PE - Protective conductor terminal block




3212302

<https://www.phoenixcontact.com/us/products/3212302>

Drawings

Connection diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Connection diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Connection diagram



with PE terminals having the same contours


PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Connection diagram




phase to phase

PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Connection diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Schematic diagram




Simple three-phase current transformer set

PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Schematic diagram



Interlinked three-phase current transformer set

PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Schematic diagram



Interlinked three-phase current transformer set with grounded star point


PTMED 6-CT/1P-PE - Protective conductor terminal block




3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram



Circuit diagram



PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram



PTMED 6-CT/1P-PE - Protective conductor terminal block




3212302


<https://www.phoenixcontact.com/us/products/3212302>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3212302>

 CSA Approval ID: 158887				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B	-	-	20 - 8	-
C	-	-	20 - 8	-
D	-	-	20 - 8	-

 EAC Approval ID: RU C-DE.BL08.B.00644				
---	--	--	--	--

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B	-	-	20 - 8	-
C	-	-	20 - 8	-
D	-	-	20 - 8	-

 EAC Approval ID: KZ7500651131219505				
---	--	--	--	--

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Classifications

ECLASS

ECLASS-13.0	27250109
ECLASS-15.0	27250109

ETIM

ETIM 10.0	EC000902
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com