

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Multi-functional energy measuring device with integrated Modbus RTU/TCP interface for measuring electrical parameters in low-voltage installations up to 690 V. (phoenixcontact.com/empro-help)

Product description

The multifunctional EMpro energy measuring devices acquire your energy data and offer numerous options for communicating the data to higher-level control and management systems. Configure and integrate your energy measuring devices in just a few steps using the web-based, user-guided installation wizard. In addition, benefit from many practice-oriented web server and device functions.

Your advantages

- Energy measurement in just three steps with the intuitive installation wizard
- Easy commissioning and service with intelligent web server and display functions
- Data protection through the targeted deactivation of key configuration functions and interfaces
- Fast integration into control and management systems with future-oriented communication solutions and digital services

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 2907980 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | C446 |
| Product key | CMMC21 |
| GTIN | 4055626260570 |
| Weight per piece (including packing) | 336.4 g |
| Weight per piece (excluding packing) | 293.2 g |
| Customs tariff number | 90303100 |
| Country of origin | DE |

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

Technical data

Product properties

| | |
|-------------------------|-------------------------|
| Product type | Energy measuring device |
| Product family | EMpro |
| Number (Ethernet ports) | 1 |

Display

| | |
|--------------|---|
| Display type | LCD display, backlit, 2-color, multi-line |
|--------------|---|

Electrical properties

| | |
|---|---|
| Maximum power dissipation for nominal condition | 10 VA |
| Mains type | 3-phase (3 or 4-conductor), 2-phase (2-conductor), and single-phase (1-conductor) |

Electrical isolation

| | |
|--------------------------------------|-----------------------|
| Test voltage (reinforced insulation) | 4 kV AC (50 Hz, 60 s) |
| Pollution degree | 2 |

Electrical isolation Housing against all potentials IEC 61010-1

| | |
|-----------------------|---------------------------------|
| Standards/regulations | IEC 61010-1 |
| Overvoltage category | III (300 V AC) II (600 V AC) |
| Insulation | Reinforced insulation |

Electrical isolation Supply against all other potentials IEC 61010-1

| | |
|-----------------------|---------------------------------|
| Standards/regulations | IEC 61010-1 |
| Overvoltage category | III (300 V AC) II (600 V AC) |
| Insulation | Reinforced insulation |

Electrical isolation Voltage measurement input against all other potentials IEC 61010-2-030

| | |
|-----------------------|---------------------------------|
| Standards/regulations | IEC 61010-2-030 |
| Measuring category | III (300 V AC) II (600 V AC) |
| Insulation | Reinforced insulation |

Electrical isolation Current measurement input against all other potentials

| | |
|------------|-----------------------|
| Insulation | Functional insulation |
|------------|-----------------------|

Electrical isolation Digital I/Os

| | |
|------------|-----------------------|
| Insulation | Functional insulation |
|------------|-----------------------|

Electrical isolation Communication interface

| | |
|------------|-----------------------|
| Insulation | Functional insulation |
|------------|-----------------------|

Supply

| | |
|----------------------|--------------------------------------|
| Supply voltage range | 100 V AC ... 230 V AC ($\pm 20\%$) |
|----------------------|--------------------------------------|

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

| | |
|-------------------|-------------------------------------|
| | 150 V DC ... 250 V DC (± 20 %) |
| Power consumption | ≤ 4 W |
| Nominal frequency | 50 Hz ... 60 Hz (AC sine) |

Input data

Measuring data acquisition

| | |
|---|--|
| Measuring principle | True r.m.s. value measurement (seamless) |
| Frequency measuring range (Fundamental component) | 45 Hz ... 65 Hz |
| Measured value | AC sine (50 Hz/60 Hz) |
| Scanning rate | 12,8 kHz (50 Hz) / 15,4 kHz (60 Hz) |
| Number of periods | 10 (true RMS value at 50 Hz) 12 (true RMS value at 60 Hz) |
| Acquisition of harmonics | up to 63rd harmonic |

Measurement: Voltage

| | |
|---|--|
| Input name | Voltage measuring input V1, V2, V3 |
| Input voltage range direct | 18 V AC ... 690 V AC (Phase/Phase) 11 V AC ... 400 V AC (Phase/neutral conductor) |
| Input voltage range via external transformers | 60 V AC ... 2000000 V AC (primary) 60 V AC ... 400 V AC (secondary) |
| Surge voltage capacity | 760 V AC (Phase/Phase) |
| Precision | 0.2 % |
| Power consumption | < 0.5 VA |

Measurement: Current

| | |
|---|---|
| Input name | Current measurement I1, I2, I3 |
| Input current | 1 A (secondary) 5 A (secondary) |
| Measuring range | 1 A ... 20000 A (primary) |
| Overload capacity | 6 A (I_{max}) |
| Response threshold from measuring range nominal value | 10 mA (1 A) 50 mA (5 A) |
| Precision | 0.2 % |
| Current overload | 50 A for 1 s 20 A ($4 \times I_N$, continuous) |
| Power consumption | < 0.5 VA |

Measurement: Power

| | |
|-------------------------------|-------------|
| Precision | 0.5 % |
| Active energy (IEC 62053-22) | Class 0.5 S |
| Reactive power (IEC 62053-23) | Class 2 |
| ANSI C12.20 | Class 0.5 S |

Digital

| | |
|--------------------------|--|
| Description of the input | Digital input in accordance with IEC/EN 61131-2 (type 3) |
|--------------------------|--|

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

| | |
|----------------------|--|
| Number | 1 |
| Voltage input signal | 24 V DC 0 V DC ... 30 V DC |
| Current input signal | 2 mA ... 15 mA |
| Protection | 250 mA (fast-blow) |
| Protective circuit | Protection against incorrect DC connection (max. 30 V) |

Output data

Digital

| | |
|-----------------------|---|
| Output description | Digital output in accordance with IEC/EN 61131-2 (type 3) |
| Number | 1 |
| Current output signal | ≤ 100 mA |
| Voltage output signal | 24 V DC |
| Protection | 250 mA (fast-blow) |
| Protective circuit | Protection against incorrect DC connection (max. 30 V) |

Connection data

Current / voltage / supply

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 8 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 6 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 4 mm ² |
| Conductor cross-section AWG | 24 ... 10 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

Digital I/O / communication

| | |
|----------------------------------|--|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.14 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.14 mm ² ... 1.5 mm ² |
| Conductor cross-section AWG | 26 ... 14 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

RS-485

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Stripping length | 7 mm |
| Screw thread | M3 |
| Conductor cross-section rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Tightening torque | 0.5 Nm ... 0.6 Nm |

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

Interfaces

Data: Network interface - Ethernet

| | |
|------------------------|-------------|
| Communication protocol | Modbus/TCP |
| | REST (HTTP) |
| Connection method | RJ45 |
| Transmission speed | 10 Mbps |
| | 100 Mbps |

Data: Network interface - serial

| | |
|--------------------------|-------------------------|
| Communication protocol | Modbus/RTU |
| Communication standard | RS-485 |
| Connection method | Screw connection |
| Transmission speed range | 2.4 kbps ... 115.2 kbps |
| Resistance | 120 Ω (integrated) |

Dimensions

Item dimensions

| | |
|------------------|---------|
| Width | 90 mm |
| Height | 90 mm |
| Depth | 71.9 mm |
| Horizontal pitch | 5 Div. |

Material specifications

| | |
|-------|-----------------|
| Color | gray (RAL 7042) |
|-------|-----------------|

Environmental and real-life conditions

Ambient conditions

| | |
|--|-------------------------|
| Degree of protection | IP20 (Housing) |
| | IP40 (Display) |
| Ambient temperature (operation) | -25 °C ... 70 °C |
| Ambient temperature (storage/transport) | -30 °C ... 80 °C |
| Altitude | ≤ 2000 m |
| Max. permissible relative humidity (operation) | ≤ 95 % (non-condensing) |

Approvals

CE

| | |
|-------------|--------------|
| Certificate | CE-compliant |
|-------------|--------------|

UL, USA/Canada

| | |
|----------------|---------------------------|
| Identification | UL/C-UL Listed UL 61010-1 |
|----------------|---------------------------|

UL data

| | |
|----------------|------------|
| Operating mode | Indoor use |
|----------------|------------|

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

Standards and regulations

| | |
|-----------------------|--------------|
| Standards/regulations | IEC 61010-1 |
| | IEC 61326-1 |
| | IEC 61557-12 |

Mounting

| | |
|-------------------|---------------------|
| Mounting type | DIN rail mounting |
| Mounting position | Horizontal DIN rail |


EEM-MA370-R - Measuring device

2907980

<https://www.phoenixcontact.com/us/products/2907980>


Drawings

Connection diagram




Connection assignment

Connection diagram




Network type: 3PH-4W-3CT

Connection diagram




Network type: 3PH-4W-1CT

Connection diagram




Network type: 3PH-3W-3CT

Connection diagram




Network type: 3PH-3W-2CT

Connection diagram



Network type: 3PH-3W-1CT

Connection diagram




Network type: 2PH-2W-1CT

2907980


<https://www.phoenixcontact.com/us/products/2907980>

Connection diagram



Network type: 2PH-3W-2CT

Connection diagram




Network type: 1PH-2W-1CT

EEM-MA370-R - Measuring device

2907980

<https://www.phoenixcontact.com/us/products/2907980>

Schematic diagram



Operating and indication elements

1 LCD, backlit

2 Operating buttons for displaying measured values and for changing the configuration

3 Pulse LED


EEM-MA370-R - Measuring device

2907980

<https://www.phoenixcontact.com/us/products/2907980>



Schematic diagram



Mounting

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2907980>



cULus Listed

Approval ID: E357804

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27142330 |
| ECLASS-15.0 | 27142330 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002301 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 41113600 |
|-------------|----------|

EEM-MA370-R - Measuring device



2907980

<https://www.phoenixcontact.com/us/products/2907980>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| | Perfluorobutane sulfonic acid (PFBS) and its salts(CAS: n/a) |
| SCIP | 58f34caa-8150-4f25-a3cb-543dfee16673 |

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com