

PTMED 6-CT/1P-PE - Protective conductor terminal block




3212302

<https://www.phoenixcontact.com/us/products/3212302>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Protective conductor terminal block, connection method: Push-in connection, 1 level, cross section: 0.5 mm² - 10 mm², color: green-yellow



Product description

Test disconnect terminal block with plug-in zone for current transformer short circuit plug PPCT 6/...

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3212302 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE22 |
| Product key | BE2233 |
| GTIN | 4046356623193 |
| Weight per piece (including packing) | 27.605 g |
| Weight per piece (excluding packing) | 27.605 g |
| Customs tariff number | 85369010 |
| Country of origin | PL |

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Technical data

Product properties

| | |
|-----------------------|-----------------------|
| Product type | Ground terminal block |
| Product family | PTME |
| Number of connections | 2 |
| Number of rows | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 6 kV |
| Maximum power dissipation for nominal condition | 1.31 W |

Connection data

| | |
|---------------------------------|-------------------|
| Grounding foot | Yes |
| Number of connections per level | 2 |
| Nominal cross section | 6 mm ² |

1 level

| | |
|---|--|
| Connection method | Push-in connection |
| Note | Please observe the current carrying capacity of the DIN rails. |
| Stripping length | 12 mm |
| Internal cylindrical gage | A5 |
| Connection in acc. with standard | IEC 61984 |
| Conductor cross-section rigid | 0.5 mm ² ... 10 mm ² |
| Cross section AWG | 20 ... 8 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section, flexible [AWG] | 20 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.5 mm ² ... 6 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.5 mm ² ... 6 mm ² |
| Conductor cross-section flexible (2 conductors with the same cross-section, with TWIN ferrule and plastic sleeve) | 0.5 mm ² ... 1.5 mm ² |

1 level Connection cross sections directly pluggable

| | |
|---|--|
| Conductor cross-section rigid | 1 mm ² ... 10 mm ² |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1 mm ² ... 6 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 1 mm ² ... 6 mm ² |

Dimensions

| | |
|-----------------|----------|
| Width | 8.2 mm |
| End cover width | 2.2 mm |
| Height | 114.9 mm |

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

| | |
|--------------------|---------|
| Depth on NS 35/7,5 | 49.6 mm |
| Depth on NS 35/15 | 57.1 mm |

Material specifications

| | |
|---|--------------|
| Color | green-yellow |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 130 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 28 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Mechanical properties

Mechanical data

| | |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

Environmental and real-life conditions

Service life

| | |
|-----------------------------|-----|
| Insertion/withdrawal cycles | 100 |
|-----------------------------|-----|

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Spectrum | Long life test category 1, class B, body mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$ |
| ASD level | $1.857 \text{ (m/s}^2\text{)}^2\text{/Hz}$ |
| Acceleration | 0.8g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|----------------|-------------------------------------|
| Specification | DIN EN 50155 (VDE 0115-200):2008-03 |
| Pulse shape | Half-sine |
| Acceleration | 5g |
| Shock duration | 30 ms |

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

| | |
|--------------------------------|-----------------------------------|
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

Mounting


| | |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Connection diagram



with PE terminals having the same contours


PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Connection diagram




phase to phase

PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Connection diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Schematic diagram



Simple three-phase current transformer set


PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Schematic diagram



Interlinked three-phase current transformer set

PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Schematic diagram



Interlinked three-phase current transformer set with grounded star point


PTMED 6-CT/1P-PE - Protective conductor terminal block




3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram



Circuit diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block

3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram




PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Circuit diagram



PTMED 6-CT/1P-PE - Protective conductor terminal block





3212302


<https://www.phoenixcontact.com/us/products/3212302>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3212302>

|  CSA Approval ID: 158887 | | | | |
|---|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | - | - | 20 - 8 | - |
| C | - | - | 20 - 8 | - |
| D | - | - | 20 - 8 | - |

|  EAC Approval ID: RU C-DE.BL08.B.00644 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

|  cULus Recognized Approval ID: E60425 | | | | |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| B | - | - | 20 - 8 | - |
| C | - | - | 20 - 8 | - |
| D | - | - | 20 - 8 | - |

|  EAC Approval ID: KZ7500651131219505 | | | | |
|---|--|--|--|--|
|---|--|--|--|--|

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250109 |
| ECLASS-15.0 | 27250109 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000902 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

PTMED 6-CT/1P-PE - Protective conductor terminal block



3212302

<https://www.phoenixcontact.com/us/products/3212302>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com